



Technical Data Sheet

Gorilla Tape®

Product Description: Gorilla Tape is made to withstand elements in tough bonding applications. It offers superior adhesion for long lasting repairs.

Extra strong grip:

Double thick adhesive fills in gaps on rough, uneven surfaces.

Weather resistance:

Tough all-weather shell helps create a barrier against harsh elements.

Reinforced strength:

Tight woven backing makes it extra strong, but can still be ripped by hand.

Product Construction
Backing Polyethylene over cotton cloth
Adhesive Natural and synthetic rubber

Standard Sizes
35 yd. long x 1.9" wide
12 yd. long x 1.9" wide
Duct Tape To Go (Handy Roll) 30 ft. long x 1" wide
Tough & Wide 30 yd. x 2.88" wide

Physical Properties

Property	Standard	Metric	Test Method
Thickness	16.75 mils +/- 1.5	0.43 mm +/- 0.04	N/A
Adhesion to Steel	85 oz/in width	2.4 kg/25 mm	ASTM D3330
Adhesion to Backing	80 oz/in width	2.3 kg/25 mm	ASTM D3330
Tensile Strength	50 lbs/in width	22.7 kg/25 mm	ASTM D3759
Elongation	21%	21%	ASTM D3759
Service Temperature Range	Continuous up to 150°F Intermittent up to 200°F	Continuous up to 66°C Intermittent up to 93°C	N/A
Shelf-Life	At least 2 years on the roll depending upon storage conditions		

Note: The technical information and data found in this data sheet is intended only as representative and should not be used for specification purposes. The information is given in good faith, with tests conducted by Quality Assurance and Technical Service Departments. Bond strength and cure times are dependent on a number of factors including moisture content and temperature during assembly and cure, bonding material and test method. Users should determine the suitability of the product for their own purposes by their own tests.