



## 185-12

E0845090

Cable Lug KRF, 185mm2, M12



### Product Properties:

Suitable for Class 5 conductor	Yes
Suitable for Class 6 conductor	Yes
Insulated	No
Max. current (I <sub>max</sub> )	440 A
Number of mounting holes	1 .
Flange shape	Ring shape
Colour insulation	Other
Slender flange model	No
With sight-hole	Yes
Conductor category	Several
Max Temp	150 °C
Surface protection	Tinned
Material	Copper
Connecting angle	180° (horizontal)
Series	KRF/KSF (10-500mm <sup>2</sup> )

### Dimensions:

HS	13 mm
ID	21 mm
OD	27 mm
T	6 mm
P1	17 mm

<b>P2</b>	20 mm
<b>L</b>	85 mm
<b>N</b>	31 mm
<b>W</b>	39 mm
<b>MOQ</b>	25 .
<b>Unit</b>	pcs
<b>Bolt dimension (metric)</b>	12 .
<b>Nominal cross section</b>	185 mm <sup>2</sup>
<b>Series</b>	KRF/KSF (10-500mm2)

### **Approvals:**

<b>Approved according to CE</b>	Yes
<b>Approved according to UKCA</b>	Ja
<b>Approved according to DNV</b>	Yes

### **Compliance:**

<b>Conflict Minerals</b>	Contain "Tin"
<b>Extended Minerals</b>	Contain "Copper"
<b>PFAS</b>	No PFAS
<b>REACH</b>	No SVHC (Latest. 05 Nov 2025)
<b>RoHS</b>	RoHS 3 (2015/863)
<b>SCIP</b>	Not Applicable
<b>US TSCA</b>	No (5 PBT Subs, Feb 2021)
<b>ECCN (EU)</b>	No CLASS
<b>ECCN (US)</b>	EAR99

### **Other information:**

<b>ETIM-Class</b>	EC001051 - Tube cable lug for copper conductors
<b>ETIM-Release</b>	9.0
<b>Trademark</b>	NEMIQ
<b>Product Group</b>	Cable lugs
<b>Search Description</b>	EFO2024V
<b>Alternative SKU</b>	185-12
<b>E-no</b>	E0845090

### **Logistic information:**

<b>Barcode</b>	733117611993
<b>Country of origin</b>	CN
<b>E-no</b>	E0845090
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	25 .
<b>Stock code</b>	185-12

**Taric code**

85369010

---

**Unit**

pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.

---

**Nelco Contact AB** - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - [order@nelco.se](mailto:order@nelco.se) - [www.nelco.se](http://www.nelco.se)