

Angle Grinder LXT®

DGA452

18V • 115 mm • 11 000 min⁻¹

Powerful angled grinder

A 18V powerful cordless angle grinder. Standard angle grinder discs available. Slim body design for added comfort. Anti-restart function. .



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	11000 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	115 mm
Anti-Restart Function (NVR Switch)	✓
Vibration Level, Disc Sanding	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Disc Sanding	1,5 m/s ²
Vibration Level, Surface Grinding	10,0 m/s ²
Vibration Uncertainty (K Factor), Surface Grinding	1,5 m/s ²
Sound Pressure Level (L _{pA})	79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Slim body design for a good grip
- Anti-restart function minimises accidental start-up
- Electronic overload protection protects the user and the device
- Externally accessible brushes for easy serviceability
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing