


TAPD512BS - Break Stem Open

| General Part Information | | |
|-----------------------------|-------------------|---|
| Product Description | | TAPD512BS |
| Article Number | | 20134.00 |
| Rivet Type | i | Break Stem Open |
| Standard Bulk Pack Quantity | | 5000.00 |
| Application / Features | i |  |

| Geometry / Dimensions / Performance | | |
|-------------------------------------|-------------------|---------|
| Head Style | i | Domed |
| Body Diameter Ø (mm) | | 4.00 |
| Body Length (mm) | | 14.00 |
| Min. Grip Range (mm) | | 7.90 |
| Max. Grip Range (mm) | | 9.50 |
| Min. Hole Diameter (mm) | | 4.10 |
| Max. Hole Diameter (mm) | | 4.20 |
| Min. Flange Diameter (mm) | | 7.62 |
| Max. Flange Diameter (mm) | | 8.22 |
| Flange Thickness (mm) | | 1.22 |
| Mandrel Diameter (mm) | | 2.29 |
| Nominal Shear Strength (N) | | 1330.00 |
| Nominal Tensile Strength (N) | | 1910.00 |

| Material / Finish / Weight | | |
|----------------------------|-------------------|---------|
| Body Material | i | AlMg3.5 |
| Mandrel Material | | Steel |
| Finish | | Clean |
| Weight per thousand (kg) | | 1.90 |



[CONTACT US](#)

[CUSTOMIZE](#)

[PRINT](#)

[SEARCH SETTING TOOL](#)