

VARTA Work Flex® Pocket Light with 3AAA Batt.



Compact, water resistant and shock proof LED Work Light with pocket clip and magnetic mounting feature for hands-free working.



Information

- Shock Proof
- Water resistant (IP54) and shock proof
- 2 light levels: spot light and area light
- High performance LED
- Pocket clip and magnet for hands free working
- Non-slip rubber coated handle
- Dirt-resistant surface

Article Details

Ordernumber	17647 101 421
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	40.00 m
Runtime	6 h
Total light output	110 lm
Bulb Equipment	COB LED
Product Materials	Flashlights, Acrylonitrile Butadiene Styrene, Polycarbonate, Thermoplastic Rubber
Equipped with	3 x AAA Longlife Power
Product Length / Depth mm	173.00
Product Width mm	24.00
Product Height mm	31.00
Product Weight g	61.90

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 977925	100.00	35.00	230.00	0.12
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 977932	245.00	125.00	115.00	0.55
PAL (Pallet)	972	40 08496 977949	800.00	1,200.00	1,185.00	155.53
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
9	27		243		4	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

