



60104

MINIATURE CIRCUIT BREAKER 120V 3A


[Download your 60104 datasheet](#)

[Characteristics](#) | [Documents & Downloads](#)

Main

☐ Hide

Device application	Distribution
Range of product	C60
Product or component type	Miniature circuit-breaker
Device short name	C60 UL489
Poles description	1P
Number of protected poles	1
[In] rated current	3 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	10 kA AIR conforming to UL 489 - 277 V AC 50/60 Hz 10 kA Icu conforming to IEC 60947-2 - 277 V AC 50/60 Hz
Suitability for isolation	Yes conforming to IEC 60947-2 Yes conforming to UL 489

Complementary

☐ Hide

Network frequency	50/60 Hz
[Ue] rated operational voltage	120...240 V AC 50/60 Hz 125 V DC 60 V DC
Magnetic tripping limit	7...10 x In
Contact position indicator	Yes
Control type	Toggle
Local signalling	Positive break indication
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	73 mm
Product weight	0.11 kg
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Tunnel type terminals flexible wire(s) 16 mm² max Tunnel type terminals rigid wire(s) 25 mm² max
Wire stripping length	14 mm
Tightening torque	2 N.m


Environment

☐ Hide

Standards	IEC 60947-2 UL 489 CSA C22.2 No 5.2
IP degree of protection	IP40 IEC 60529
Tropicalisation	2 conforming to IEC 60068-1 2 conforming to UL 489
Relative humidity	95 % 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

Offer Sustainability

 Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1201 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  download Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

 Hide

Period	18 months
---------------	-----------