

DF2CN02

NFC cartridge fuses, Tesys GS, cylindrical 10 mm x 38 mm, fuse type gG, 500VAC, 2 A, without striker

Price* : 5.75 GBP



Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	500 V AC
[In] rated current	2 A 500 V
Fuse size	10 x 38 mm
Fuse type	NFC
Quantity per set	Set of 10

Complementary

Fuse curve	GG
Net weight	0.01 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------