

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Angle Grinder with X-LOCK

PRO GWX 18V-10 P



Improved power level and tool control in the 18 V category – with X-LOCK

The most important data

Battery voltage	18.0 V
No-load speed	9,000 rpm
Disc diameter	125 mm

Part Number 0 601 9J4 201

Technical data

Technical data

No-load speed	9,000 rpm
Battery voltage	18.0 V
Weight excl. battery	1.9 kg
Packaging dimensions (width x length x height)	370 x 445 x 160 mm
Disc diameter	125 mm

Noise/vibration information

Surface grinding (roughing)

Vibration emission value ah	6 m/s ²
Uncertainty K	1.5 m/s ²

Sanding with sanding sheet

Vibration emission value ah	3 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- Delivers power equal to a 1,000 W corded grinder due to brushless motor technology
- Changing accessories is fast and convenient thanks to keyless X-LOCK click system
- PROtection switch, Drop Control, KickBack Control, and X-Brake provide maximum user protection and convenience



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

