

Datasheet Micro USB Power Adapter 5Vdc 5W UK Plugtop RS Stock No.: 8280217

ENGLISH





Features

- Universal AC Input
- UK Plugtop
- Small & Compact Design
- Micro USB Output
- Over Voltage, Over Current & Short Circuit Protections
- ErP Level V
- RoHS Compliant
- MTBF >50,000 hours

| RS Stock Number | Manufacturers P/N | Output Voltage | Output Current (Min) | Output Current (Max) | Power (Watts) | Line Regulation | Voltage Tolerance | Ripple & Noise (mV- p-p) |
|--------------------|----------------------|-------------------|----------------------------|----------------------------|------------------|-----------------|----------------------|--------------------------------|
| 8280217 | T5586ST | +/- 5Vdc | 0A | 1A | 5W | +/-3% | +/-5% | 200mV |

Input

- Rated Input 100-240Vac
- Rated Input Frequency 50-60Hz
- Input Current 0.2A
- Leakage Current 0.25mA
- UK Plugtop

Output

• 1.5M Lead with Micro USB

Enivronmental

- Operating Temperature 0°C to 40°C
- Storage Temperature -20°C to 60°C
- Operating Humidity 20% to 85%
- Storage Humidity 5% to 95%

Casing

- Dimensions 67mm x 49.55mm x 64.8mm
- Weight 80g (approx.)

