

**Passeinsatz für Einsätze E14 4 A
DIGI CHECK PRO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

General ordering data

| | |
|------------|--|
| Order No. | 9918870000 (14mm tips); 9201580000 (2mm tips) |
| Type | DIGI CHECK PRO |
| Version | Digital voltage tester, Yes, +2.5 k Ω upon pressing the LOAD key, \geq 300 k Ω |
| GTIN (EAN) | 4032248405756 |
| Qty. | 1 pc(s). |

Passeinsatz für Einsätze E14 4 A DIGI CHECK PRO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions

| | |
|--------|-------|
| Weight | 290 g |
|--------|-------|

Technical data

| | |
|---------|----------------|
| Version | Protective bag |
|---------|----------------|

Product data

| | | | |
|---------------------------|--|----------------------------------|--|
| Rated voltage, min. | 5 V AC/DC | AC voltage measuring range | 5-690 V |
| Frequency range, min. | 0 Hz | Frequency range, max. | 100 Hz |
| Rated voltage, max. | 690 V AC/DC | Protection degree | IP 65 |
| Battery type | 1.5 V type AAA battery | Tested and approved according to | EN/IEC 61243-3 :2010-10 (VDE 0682 part 401) |
| Input resistance, voltage | +2.5 k Ω upon pressing the LOAD key, \geq 300 k Ω | Peak voltage resistance | 8 kV |
| Display | LCD | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 2.0 | EC000494 | ETIM 3.0 | EC000494 |
| UNSPSC | 41-11-36-37 | eClass 4.1 | 27-20-03-08 |
| eClass 5.1 | 27-20-03-08 | eClass 6.0 | 27-20-03-08 |
| eClass 7.0 | 27-20-03-08 | | |

Product information

| | |
|--------------------------------|--|
| Descriptive text ordering data | Protective case included |
| Description of article | Voltage tester up to 690 V/ 2000 Hz LCD |
| Product description | <ul style="list-style-type: none"> • Test probe illumination • Selectable load for residual current test • Phase sequence indicator |

Approvals

Approvals

**Passeinsatz für Einsätze E14 4 A
DIGI CHECK PRO**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Drawings

