



Wire Harness Tape – Strong, High Temperature Cloth Tape

HelaTape Protect 250

Features and Benefits

- High temperature Polyester Fabric harnessing tape
- Special acrylate-based adhesive offers very good heat and media resistance
- Very high temperature stability from -40 °C to +150 °C
- Temperature and humidity resistance tested according to LV312
- Very good resistance against abrasion
- Material is very flexible and easy to handle
- Excellent ageing resistance, stable against rotting
- Provides long term reliability under varying and extreme environmental conditions



HelaTape Protect 250 is designed for cable harnessing and offers a very high temperature resistance.

MATERIAL	Polyester (PET)
Operating Temperature	-40 °C to +150 °C
Adhesion to Steel	2.5 N/10 mm
Adhesion to Backing	2 N/10 mm
Elongation at break	15 %
Breaking Strength	180 N/10 mm



HelaTape Protect 250

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-PROTECT250	0.25	19.0	25.0 m	Black (BK)	712-10003

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.