



SAFETY DATA SHEET
CHAIN & DRIVE FLUID

Page: 1

Compilation date: 02/12/2014

Revision date: 15/05/2018

Revision No: 6

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: CHAIN & DRIVE FLUID

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC24: Lubricants, greases, release products.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Irrit. 2: H319; -: EUH208

Most important adverse effects: Contains long chain alkyl amine, long chain alkyl acid. May produce an allergic reaction.
Causes serious eye irritation.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains long chain alkyl amine, long chain alkyl acid. May produce an allergic reaction.

H319: Causes serious eye irritation.

Hazard pictograms: GHS07: Exclamation mark



Signal words: Warning

[cont...]

SAFETY DATA SHEET

CHAIN & DRIVE FLUID

Page: 2

Precautionary statements: P264: Wash hands thoroughly after handling.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+313: If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

SOLVENT REFINED BASE OIL (NOTE L - LESS THAN 3% DMSO EXTRACT) - REACH registered number(s): 01-2119480472-38

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-166-0	64742-62-7	Substance with a Community workplace exposure limit.	-	30-50%

MINERAL OIL (NOTE L - LESS THAN 3% DMSO EXTRACT)

265-090-8	64741-88-4	Substance with a Community workplace exposure limit.	-	30-50%
-----------	------------	--	---	--------

CALCIUM DINONYLNAPHTHALENESULPHONATE - REACH registered number(s): 01-2119980985-16

939-717-7	-	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319	1-10%
-----------	---	---	---	-------

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

224-235-5	4259-15-8	-	Eye Dam. 1: H318; Aquatic Chronic 2: H411	1-10%
-----------	-----------	---	---	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.
Eye contact: Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.
Ingestion: Wash out mouth with water.
Inhalation: Move to fresh air in case of accidental inhalation of vapours. Seek medical attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.
Eye contact: There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.
Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

[cont...]

SAFETY DATA SHEET

CHAIN & DRIVE FLUID

Page: 3

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: No data available.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS. Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

[cont...]

SAFETY DATA SHEET

CHAIN & DRIVE FLUID

Page: 4

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	-	5 mg/m ³	-	-

MINERAL OIL (NOTE L - LESS THAN 3% DMSO EXTRACT)

UK	5mg/m ³	10mg/m ³	-	-
----	--------------------	---------------------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Tightly fitting safety goggles. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Yellow-brown

Odour: Characteristic odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Viscosity: Non-viscous

Boiling point/range°C: >150

Melting point/range°C: < -20

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: > 150

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: > 150

Vapour pressure: No data available.

Relative density: 0.93

pH: No data available.

VOC g/l: No data available.

[cont...]

SAFETY DATA SHEET

CHAIN & DRIVE FLUID

Page: 5

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: No data available.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

DERMAL	RBT	LD50	>5000	mg/kg
ORAL	RAT	LD50	>3100	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

Other information: Not applicable.

[cont...]

SAFETY DATA SHEET

CHAIN & DRIVE FLUID

Page: 6

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

ALGAE	72H ErC50	>240	mg/l
DAPHNIA	48H EC50	1 - 10	mg/l
FISH	96H LC50	1 - 10	mg/l

12.2. Persistence and degradability

Persistence and degradability: Not readily biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: No data available

Waste code number: 13 02 05

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: No data available

[cont...]

SAFETY DATA SHEET

CHAIN & DRIVE FLUID

Page: 7

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: EC Directive 1999/45/EC relating to the classification, packaging and labelling of dangerous preparations.

EC Directive 91/155/EEC defining the laying down and detailed arrangements for the system of specific information relating to dangerous preparations.

Phrases used in s.2 and s.3: EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H315: Causes skin irritation.

H318: Causes serious eye damage.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

