

# Datasheet

## Check Valve

RS Stock Number [458-6788](#)



### Features

- Permits flow in one direction only
- Body and shut-off valve in stainless steel 316L
- Spring in stainless steel 302
- 'O'-rings fluorelastomer FKM (FPM)
- Maximum working pressure 40 bar
- Temperature range -20°C to +180°C

### Specifications

- |                            |                 |
|----------------------------|-----------------|
| • Body Material            | Stainless Steel |
| • Connection               | ¼ in G          |
| • Maximum Working Pressure | 40bar           |
| • Thread Size              | ¼ in            |
| • Thread Standard          | G               |
| • Type                     | Single          |

### Measurements

- |                |       |
|----------------|-------|
| • C :          | G1/4  |
| • F (mm):      | 17    |
| • ØG (mm):     | 22    |
| • L (mm):      | 50    |
| • Weight (kg): | 0.074 |

