

## ROUND LED BULKHEAD - EMERGENCY



MLA part code	BL12LEDE	BL20LEDE
<b>Description</b>	LED Bulkhead with emergency	
<b>ErP Class</b>	A+	A
<b>Weight (kg)</b>	1.20	1.25
<b>Wattage (W)</b>	12	20
<b>Lumens (lm)</b>	1071±5%	1600±5%
<b>Efficacy (lm/W)</b>	89	80
<b>Beam Angle (°)</b>	112	111
<b>Overall dimensions (mm)</b>	305 (d) 84 (p)	400 (d) 96 (p)
<b>CCT</b>	4000K	
<b>LED Colours</b>	Cool White	
<b>Input voltage</b>	Mains 230V 50Hz	
<b>Construction</b>	Polycarbonate	
<b>Class</b>	Class II double insulated	
<b>IP rating</b>	IP54	
<b>Warranty</b>	3 Years	
<b>Photometric data</b>	Yes	
<b>Dimmable</b>	No	
<b>Instruction sheet</b>	Yes	
<b>Origin of Manufacture</b>	China	
<b>Quality assurance system</b>	ISO9001	
<b>Declaration of Conformity (held on file)</b>	Yes	
<b>Manufactured &amp; accordance with</b>	EN60598	

