

Datasheet

RS Pro Panel Mount, Snap In Mount Outlet Connector, Female, 6 Way, 20A, 250 V ac

RS Stock No: **896-2133**



Product Details

RS Pro IEC socket C13 variant, snap in panel mount outlet connectors with nylon 6 body and tin plated copper alloy mating contacts and faston terminals. These C13 connectors offers a hard wearing durable solution for many applications that require IEC C13 snap in panel mount socket connectors.

Features and Benefits

- HV Breakdown Test for 1 Minute: 2 KV ac
- Insulation Resistance at 500 V dc 1000 MΩ min
- Permissible Temperature with/without load: 0 to 70°C
- Contact Resistance 10 MΩ max

Specifications:

Body Orientation	Straight
Contact Material	Copper Alloy
Contact Plating	Tin
Current Rating	20 A
Gender	Female
Mounting Type	Panel Mount, Snap-In Mount
Number of Contacts	6
Number of Rows	2
Termination Method	Faston
Type	Outlet Connector
Voltage Rating	250 V ac
Body Material	20% Glass Filled Nylon 66, V2
Breakdown Voltage	2 kV ac
Contact Resistance	10 mΩ
Dimensions	51 x 35 x 32.5 mm
Insulation Resistance	1000 MΩ
Standards Met	IEC 60320-1; UL 498; CSA C22.2 No. 182.3