

FEATURES

- **Grey Colour:** Blends seamlessly into industrial environments
- **DC Current Type:** Ensures compatibility with DC power systems
- **ABS Housing:** Provides durability and resistance to impact
- **IP43 Rating:** Offers protection against solid objects and water spray
- **Maximum Operating Temperature of 50 °C:** Suitable for a range of environments
- **Maximum Sound Level of 92 dB:** Loud enough to be heard in noisy settings
- **24 V DC Maximum Supply Voltage:** Compatible with standard DC power supplies
- **Wall Mount Type:** Easy to install in various locations
- **Steady Tone Type:** Provides a consistent and clear alert

RS PRO Grey DC Horn, ABS Housing

RS Stock No: 658-305



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO horn is designed for use in environments where a clear and consistent sound signal is required. It operates on DC current and is ideal for industrial settings where reliable audio alerts are necessary. The horn's main benefit is its ability to deliver a steady tone, ensuring that alerts are unmistakable and effective.

General Specifications

Colour	Grey
Mount Type	Wall
Number of Tones	1
Product Type	Horn
Tone Type	Steady

Electrical Specifications

Current Type	DC
Maximum Supply Voltage	24 V dc

Mechanical Specifications

Housing Material	ABS
------------------	-----

Protection Category

IP Rating	IP43
-----------	------

Operation Environment Specifications

Maximum Operating Temperature	50 °C
-------------------------------	-------

Measurement Specifications

Maximum Sound Level	92 dB
---------------------	-------

Approvals

Standards/Approvals	CE, EAC
---------------------	---------