



Foot protection

FROST OB SRA

AGRICULTURE-GREEN AREAS

Fur-lined work boot offering ideal thermal insulation, equipped with a lace-up collar to adjust the upper



Specific benefits



Comfort

- Flexible sole to reduce fatigue during use
- Lightweight product to reduce fatigue throughout the day
- Ergonomically designed footwear for comfortable wear



Performance

- Grip on the ground



Easy to use

- Drawstring to ensure watertightness



Durability

- Sustainable materials

Applications

- Agriculture
- Public works
- Forestry

Certifications and norms



EN ISO 20347

OB SRA

Protects against risks



Cold



Slip



Weather



Foot protection

FROST OB SRA

AGRICULTURE-GREEN AREAS

Fur-lined work boot offering ideal thermal insulation, equipped with a lace-up collar to adjust the upper

Standards - Details

Technical details

Shoe type	Half-boot
Outsole material	PVC
Anti-perforation insert	None
Upper material	PVC
Upper height size 42 (cm)	35
Calf circumference (cm)	47
Lining material	Textile, Polyester, Synthetical-fur
Outsole finition	Injected
Weight (g per shoe)	1100
Size range	36 → 47



Safety footwear

FROST OB SRA

AGRICULTURE-GREEN AREAS

Fur-lined work boot offering ideal thermal insulation, equipped with a lace-up collar to adjust the upper

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
FROSTOBVE36	Green-Black	36	FROST OB SRA	3295249258290	13295249258297	8	1	14.9 kg	39.8 cm	40.2 cm	57.6 cm
FROSTOBVE37	Green-Black	37	FROST OB SRA	3295249259594	13295249259591	8	1	15.1 kg	40.6 cm	41.8 cm	56.6 cm
FROSTOBVE38	Green-Black	38	FROST OB SRA	3295249259600	13295249259607	8	1	15.9 kg	39.6 cm	39.8 cm	57.6 cm
FROSTOBVE39	Green-Black	39	FROST OB SRA	3295249259617	13295249259614	8	1	16.0 kg	39.8 cm	40.2 cm	57.2 cm
FROSTOBVE40	Green-Black	40	FROST OB SRA	3295249259624	13295249259621	8	1	14.9 kg	40.2 cm	40.8 cm	57.6 cm
FROSTOBVE41	Green-Black	41	FROST OB SRA	3295249259631	13295249259638	8	1	16.9 kg	40.0 cm	40.0 cm	57.8 cm
FROSTOBVE42	Green-Black	42	FROST OB SRA	3295249259648	13295249259645	8	1	17.9 kg	38.4 cm	40.0 cm	58.0 cm
FROSTOBVE43	Green-Black	43	FROST OB SRA	3295249259655	13295249259652	8	1	18.1 kg	38.8 cm	40.2 cm	58.2 cm
FROSTOBVE44	Green-Black	44	FROST OB SRA	3295249259662	13295249259669	8	1	18.9 kg	40.2 cm	42.0 cm	56.8 cm
FROSTOBVE45	Green-Black	45	FROST OB SRA	3295249259679	13295249259676	8	1	17.8 kg	39.4 cm	40.4 cm	57.4 cm
FROSTOBVE46	Green-Black	46	FROST OB SRA	3295249259686	13295249259683	8	1	20.4 kg	40.0 cm	40.6 cm	57.4 cm
FROSTOBVE47	Green-Black	47	FROST OB SRA	3295249261290	13295249261297	8	1	18.2 kg	40.0 cm	40.0 cm	48.7 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height