2104 : Stainless Steel Pipe Cutter 14-54 mm
















Description

Max thickness: 3.2 mm.
Soft Touch® non-slip knob: good hold in hand.
Quick and tool-less wheel change.

References

Sku	A mm	A " OD	L mm	H mm	E maxi mm	kg
210475	14 - 54	1/2 - 2.1/8	185	79	3,2	0,555

