

Datasheet

Steel Diagonal Cutter

RS Stock number [497-007](#)



Description:

Constructed from high grade steel with mirror polish and slip guard
Two component handle for ease of use
VDE tested and confirms to IEC 900 1000V
Made in Germany
For soft and piano wire (P)
Power joint and precision cutting edges for hardest and enduring use
Cutting edge with external bevel

Specifications:

| | |
|-------------------------------------|----------|
| Cutting Capacity (Piano Wire): | 2.3 mm |
| Cutting Capacity (Soft Steel Wire): | 2.7 mm |
| Material: | Steel |
| Maximum Cutting Capacity: | 2.7 mm |
| Overall Length: | 180 mm |
| Type: | Diagonal |