



PRODUCT-DETAILS

UPS PowerValue 11T G2 3 kVA S

UPS PowerValue 11T G2 3 kVA S



General Information	
Extended Product Type	UPS PowerValue 11T G2 3 kVA S
Product ID	4NWP100162R0002
EAN	7640169261930
Catalog Description	UPS PowerValue 11T G2 3 kVA S
Long Description	VFI online double conversion;2700W;0min(long backup);RS232;USB;mini COM slot

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD003869
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	cded5fbc-b457-4abd-ba2f-05cb4d408fd8 Switzerland
Simplified SCIP	19ff5d38-3e67-4162-97b8-4a1666d61f06 Spain 2395317f-1956-4a09-8745-816a2beec42f Belgium 75e412ec-4a79-4983-b5b1-89011ea189b1 Netherlands e7342c6f-e813-4b08-92d4-bd4c178befc9 Hungary

f6fa3999-e477-4820-af63-d23189bbdeed	Poland
1265a8d2-7166-4ec3-a0be-77d32a1233a3	Bulgaria
6d4edaf5-f34e-4522-b077-b958910bf19b	France
317771e7-676f-44e1-8539-769039f3aa18	Hungary
9366e315-7eb8-449b-9fa9-6ea3dd0b5784	Germany
7a9fe0a6-c903-4807-b99d-563591808af6	Croatia
015e1542-c534-4866-88b2-41df344f2b3f	Czech Republic
cbd94ebd-f17d-4403-b290-6a12472ccb1d	Germany
4b2f11c4-a74e-4c5b-b8ae-2427c900eb88	Germany
239ba48c-9b1f-4e48-8eb9-3f3b04fe9e34	Finland
07b3be4e-5c37-4a98-93ed-446e3e0b4816	Norway
2d49e50b-03a3-42e9-8b86-34fc3c02b647	Estonia
cc758580-1f1f-44a7-99eb-4bec3b6395ce	Poland
db66d7f1-a835-4657-98d1-307a71359f26	Greece
a466be7b-c827-4f86-a9de-6d612d8682d4	France
94b6b481-cb81-4b93-a2c4-2531011e34cb	Portugal
4a698f3a-7001-48be-b12a-84f559c6feal	Sweden
df4522b6-91e9-4f20-aeb5-4980f7f02c8d	Belgium
d746813b-3b1e-4bd0-ac0d-607f2b6d17fd	Germany
59ccfd86-7a63-41d7-9a56-14b84f7e3fb6	Denmark
fd8216ea-5f29-4cb8-a6cd-44df2d8c4379	Sweden
907f2b54-10ad-42e4-b605-2e98844fb614	Germany
33c14b0c-d374-4422-8728-d60f07442b64	Poland

Popular Downloads

Data Sheet, Technical Information	4NWD003883_EN
Instructions and Manuals	4NWD003883_EN

Environmental

Environmental Information	No declaration needed
---------------------------	-----------------------

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408624
E-Number (Norway)	6609405
E-Number (Sweden)	5257250
Country or Territory of Origin	China

Dimensions

Product Net Width	102 mm
Product Net Height	327 mm
Product Net Depth / Length	390 mm
Product Net Weight	6.0 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	194 mm

Package Level 1 Height	456 mm
Package Level 1 Depth / Length	488 mm
Package Level 1 Gross Weight	7.0 kg
Package Level 1 EAN	7640169261930

Technical

Apparent Power Output	3000 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.5 kg
Communication Interface	USB, RS-232
Connection Type	IEC C20
Input Voltage (U _{in})	220 V 230 V 240 V
Input Voltage Type	AC
Number of Batteries	4
Number of Outputs	C13 Connection 3 Fixed Connections 1
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function Potential free switch contact Network-management
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	2700 W

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD003869

External Classifications and Standards

ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 T G2 IEC 230V

