

Datasheet

ENGLISH

RS PRO Panel Mounting printer

Stock No: 178-5733



This RS Pro panel mount printer features a Seiko brand fixed head thermal line printer mechanism with a guillotine auto-cutter and anti-blockage design. It also has a large paper capacity. It has an electrical rating of 24VDC/2A and an RS232 + USB Interface.

This printer has a resolution of 8dpmm with 576 dots per line. Effective printing width 72mm. Print speed 170mm/s.

Features and Benefits

Partial/full auto-cut

Simple drop-in easy paper loading for operational efficiencies

Data input is USB 2.0 full-speed, RS-232 serial

Compact dimensions; Height 132mm, of 125.5mm, depth 87mm

Paper width is 79.5mm (+/- 0.5mm)

Reliable long-life expectancy of MCBF 1 million lines.

Robust, stylish design that is easily embedded into many devices.

Applications

Receipt printing

Medical/Healthcare equipment

POS Receipt printing

OEM Machines

Test and measurement