

BIZ2 - Bizweld Work FR Jacket

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton, 330g

Outer Carton: 22

Product information

The Bizweld FR Jacket provides the wearer with all day protection and comfort. Features include secure stud fasteners down the front and two chest pockets with flaps. This flame resistant jacket also includes a concealed mobile phone pocket.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

EN 61482-2 EN 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Chest pockets with stud flap closure
- Stud adjustable cuffs for a secure fit
- Concealed stud front for easy access
- External standards label for quick identification of protection levels
- Available in sizes from XS to 5XL
- Radio loop for easy clipping of a radio
- Concealed phone pocket
- 3 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays

BIZ2 - Bizweld Work FR Jacket

Commodity Code: 6203321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/12872-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	DUN14
BIZ2NVRXS		58.0	38.0	28.0	0.6720	0.0617	5036108243617	15036108731852
BIZ2NVRXS		58.0	38.0	28.0	0.7290	0.0617	5036108046379	15036108607843
BIZ2NVRM		58.0	38.0	28.0	0.7660	0.0617	5036108046386	15036108607836
BIZ2NVRL		58.0	38.0	28.0	0.7810	0.0617	5036108046393	15036108607829
BIZ2NVRXL		58.0	38.0	30.0	0.8330	0.0661	5036108046409	15036108607850
BIZ2NVRXXL		58.0	38.0	30.0	0.8710	0.0661	5036108046416	15036108607867
BIZ2NVRXXXL		58.0	38.0	30.0	0.8810	0.0661	5036108046423	15036108607874
BIZ2NVR4XL		58.0	38.0	30.0	0.9180	0.0661	5036108046430	15036108607812
BIZ2NVR5XL		58.0	38.0	30.0	0.9270	0.0661	5036108216475	15036108703675