

Electronic Components
KEMET
CHARGED.®

[illegible]

General Information	
Series:	SSR10V/H
Style:	Through-Hole
Features:	Small Standard Common Mode, High Permeability, Compact Size, Low Profile, Light Weight, High Impedance, Strong Inductance
RoHS:	Yes
Miscellaneous:	55 (K) Temperature Rise Max.

Specifications	
Voltage AC:	250 VAC
Inductance:	22 mH (10 kHz)
Current:	800 mA
Temperature Range:	-25/+120°C
DC Resistance:	650 mOhms

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	600
Weight:	9 g

Electronic Components
KEMET
CHARGED®