

### MV70 - Modaflame Rain Multi Norm Arc Jacket

**Collection:** Modaflame™ Rain+ HV

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Modaflame Rain+ HV: 98% Polyester, 2% Carbon Fibre, PU Coated, bonded to 60% Modacrylic, 40% Cotton

**Outer Carton:** 8

### Product information

The Modaflame Rain Multi Norm Arc Jacket is constructed from high quality fabrics and trims. Designed to give the highest rated protection combining hi vis, flame resistant, chemical resistant, anti static, waterproof and ARC rated properties. Using an up-to-date ergonomic design, this jacket has a great fit.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.



### Standards

EN ISO 11612 (A1 + A2, B1, C1, E3, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-2 APC 2

IEC 61482-2 IEC 61482-1-1 (ELIM 32 CAL/CM², ATPV 39 CAL/CM² )

EN 13034 Type 6

EN ISO 20471 Class 3

RIS 3279 TOM Issue 2 (Orange Only)

EN 343 Class 3:1 X

### Features

- Protection against radiant, convective and contact heat
- Waterproof and breathable with taped seams to prevent water penetration
- Internal pockets for safe storage
- FR cotton lined for added warmth and comfort
- Pre-bent sleeves allow for increased freedom of movement
- Hook and loop cuffs for a secure fit
- Storm flap front to protect against the elements
- Anti-static
- 9 pockets for ample storage
- Detachable hood
- Interactive zip for added functionality



## PRODUCT SPECIFICATION & TECHNICAL DATASHEET

### MV70 - Modaflame Rain Multi Norm Arc Jacket

**Commodity Code: 6210200010**

#### Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/15211-04/E00-00

#### Wash Care



#### Carton Dimensions/Weight

| Item        | Colour      | Len  | Wid  | Hgt  | Weight(Kg) | Cubic(m <sup>3</sup> ) | EAN13         | GTIN/DUN14     |
|-------------|-------------|------|------|------|------------|------------------------|---------------|----------------|
| MV70ONRS    | Orange/Navy | 65.0 | 45.0 | 47.0 | 0.6160     | 0.1375                 | 5036108330461 | 25036108819267 |
| MV70ONRM    | Orange/Navy | 65.0 | 45.0 | 47.0 | 0.8030     | 0.1375                 | 5036108330454 | 25036108819250 |
| MV70ONRL    | Orange/Navy | 65.0 | 45.0 | 47.0 | 0.7680     | 0.1375                 | 5036108330447 | 25036108819243 |
| MV70ONRXL   | Orange/Navy | 65.0 | 45.0 | 47.0 | 0.5830     | 0.1375                 | 5036108330478 | 25036108819274 |
| MV70ONRXXL  | Orange/Navy | 65.0 | 45.0 | 47.0 | 0.5620     | 0.1375                 | 5036108330485 | 25036108819281 |
| MV70ONRXXXL | Orange/Navy | 65.0 | 45.0 | 47.0 | 0.6530     | 0.1375                 | 5036108351862 | 25036108840483 |
| MV70ONR4XL  | Orange/Navy | 65.0 | 45.0 | 47.0 | 0.7170     | 0.1375                 | 5036108351855 | 25036108840476 |