
Technical datasheet







CC 22

E1621602

Cable Cutter 1-Handed with Stripping Blade 0.2-35mm2, Box

Product Properties:

Grip design	1-component
With impact protection	No
Suitable for steel wire braiding	No
Replaceable cutting head	No
Cutting jaws exchangeable	No
With strip function	Yes
Insulated	Yes
Suitable for solid conductors	Yes
Suitable for stranded conductors	Yes
Suitable for fine strand conductors	Yes
Construction/operation	Mechanic one hand
Isolation protection 1000 V	No
With spring	No

Dimensions:

Max. cable cross section	35 mm²
MOQ	1 .
Unit	pcs
Suitable for max. cable diameter	10 mm
Total length	162 mm

Approvals:

VDE tested	No

Isolation protection 1000 V	No

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	In compliance
PFAS	No PFAS
REACH	No SVHC (250 Subs. 25 June 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	N/A
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000142 - Cable shears
ETIM-Release	10.0
Trademark	NEMIQ
Warranty	1 years
Product Group	303000
Search Description	CCTOOLS CC22 CC-22 BLÅTÅNGEN
Alternative SKU	CC22
E-no	E1621602

Logistic information:

Barcode	733117631018
Country of origin	JP
E-no	E1621602
Item status	Order
MOQ	1 .
Stock code	CC 22
Taric code	82032000
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.