

Product data sheet

Characteristics

25CJB4W

Mita - 2-way angle box - for 25 mm conduit - white



Main

Range of product	Mita
Product or component type	Junction box
Colour tint	White
Quantity per set	Set of 10

Complementary

Cable entry	2 tube entry
Junction box type	Angle
Product destination	Diameter: 25 mm conduit
Product compatibility	Insert clip when used to suspend lighting units
Maximum load	3 Kg at 60 °C
Material	UPVC (unplasticized polyvinyl chloride)

Environment

Standards	BS 4607-5
-----------	-----------

Packing Units

Package 1 Weight	1.000 G
Package 1 Height	1.000 Mm
Package 1 width	1.000 Mm
Package 1 Length	1.000 Mm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**