

Previously known as: Sensilite®



Multi Purpose



Light Duty

## Palm-coated light-duty industrial gloves

- **Improved durability:** Thanks to robust polyurethane coating around the palm area, these light-duty gloves boast excellent durability, satisfying EN level 4 abrasion resistance standards
- **Elevated comfort:** Designed with a seamless construction and available in a wide range of sizes, these HyFlex® gloves also deliver an optimal fit and high levels of wearer comfort



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

### Applications

- Final assembly of dashboard, cables and wires
- Final assembly of electronic components and mother boards

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 48-130

Light-duty ESD glove

Previously known as: Sensilite®

### Key Features

- **Polyurethane palm coating:** Strong mechanical resistance and durability
- **Seamless construction and varied sizes:** Optimized fit and comfort

### Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance



### Technologies



**Touchscreen Compatible**

### Specifications

| BRAND   STYLE  | DESCRIPTION                                                                                                                            | Gauge | SIZE           | LENGTH                        | COATING COLOR | PACKAGE                      |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------|-------|----------------|-------------------------------|---------------|------------------------------|
| HyFlex® 48-130 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Polyurethane<br><b>Liner Material:</b> Nylon<br><b>Cuff Style:</b> Knitwrist | 15    | 6, 7, 8, 9, 10 | 205-255 mm; 8.07-10.04 inches | White         | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

# Ansell