

Datasheet

RS PRO enclosure, PC, 201x163x98mm

Stock No: 197-2027



Sample photo

Technical Specifications:

Material	Polycarbonate
Dimensions (LxWxH)	201x163x98mm
Colour	Base: RAL 7035 – light grey Cover: RAL 7035 – light grey
IP Rating	IP 65
IK Rating	IK 07/IK08
Electrical insulation	Totally insulated
Flammability Rating	UL 746C 5"

Features & Benefits:

- Quickly assembled with rapid hinge
- Compatible with all standard PVC enclosures
- Halogen free
- Good chemical resistance
- Temperature Range from -40° to $+120^{\circ}$, short term
- Temperature Range from -40° to $+80^{\circ}$, continuous
- Including:

Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensional line drawings

