

Eaton 12TDLEJ25

Catalog Number: 12TDLEJ25

Eaton Bussmann series medium voltage DIN fuse, 25 A, AC 12 kV, 2", 51 x 292 mm, backup, DIN, with striker

General specifications



Product Name

Eaton Bussmann series medium voltage
DIN fuse

Catalog Number

12TDLEJ25

EAN

5027590516419

UPC

051712186070

Product Length/Depth

292 mm

Product Height

54 mm

Product Width

51 mm

Product Weight

1568 g

Compliances

DIN 43625

VDE 0670-4

IEC 60282-1

Certifications

UL

VDE

Product specifications

Used with

270303 Fuse clip

A3354710 Fuse clip

Type

Fuse

Special features

Back-up, Transformer protection, Indoor or outdoor use

Application

transformer protection

indoor or outdoor use

Amperage Rating

25 A

Fuse indicator

With Striker

Fuse size

51 x 292 mm

Breaking capacity

63 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

Resources

Technical data sheets

[720104 12kV DIN medium voltage fuses](#)

[720106 24kV DIN medium voltage fuses](#)

[720105 17.5kV DIN medium voltage fuses](#)

AC

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Pre arc (I²T)

8.1 x 100

Resistance

31.2 Ohms

Watt losses

24 W

Fuse diameter

51 mm

Color

Brown

Interrupt rating

63 kAIC

Construction size

51 x 292 mm

Mounting method

Clip-in

Packaging type

Standard

Quantity

1

Voltage rating

12 kV

Fuse type

TDLEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)