

## Datasheet

### **RS Pro White 10 A White Plate Switch Rocker Wall 7 mm, 2 Way Screwed Matte, 1 Gang BS Standard, 250 V 86mm Not Illuminated IP20**

RS Stock No: **775-8090**



## Product Details

RS Pro rocker wall light switch is current rated for 10 A and voltage rated for 250 V. This 2-way, screwed switch in white colour, has urea formaldehyde construction with matte finish for added durability. The 1-gang switch plate measures 7 x 56 mm. It includes a bag of fixing screws and white plastic screw head caps for easy installation.

## Features and Benefits

- 2-Way
- 1-Gang
- BS standard
- IP20 rated

**Specifications:**

Colour Shade	White
Colour	White
Current Rating	10 A
Faceplate Depth	7 mm
Faceplate Fixing	Screwed
Finish	Matte
Fixing Standard	BS Standard
Height	22 mm
Illumination	Not Illuminated
IP Rating	IP20
Length	85.6 mm
Material	Urea Formaldehyde
Minimum Box Depth	25 mm
Mount Type	Wall
Number of Gangs	1
Number of Poles	1
Number of Ways	2
Switch Type	Rocker
Termination Type	Screw
Voltage Rating	250 V
Width	85.6 mm