


## FEATURES

- **IP66 Rating:** Offers protection against dust and powerful water jets, making it suitable for outdoor use.
- **12.5 A Driver Current:** Delivers a stable current to ensure optimal LED performance.
- **200-240 V AC Input Voltage:** Compatible with standard AC power supplies, providing flexibility in installation.
- **Constant Voltage Operation:** Ensures consistent light output and extends the lifespan of LED fixtures.
- **Multiple Dimming Operations:** Supports leading edge, PWM, and trailing edge dimming for versatile lighting control.
- **Single Output:** Simplifies installation and reduces wiring complexity.
- **CE and EN Standards Approved:** Complies with international safety and performance standards.

## RS PRO 150W LED Driver, IP66 Rated

RS Stock No: 642-794



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This RS PRO LED Driver is designed to provide reliable power to LED lighting systems. With a maximum output power of 150W and an IP66 rating, it is ideal for both indoor and outdoor applications. The driver supports a constant voltage operation mode, ensuring consistent performance across various lighting setups.

### General Specifications

Dimming Operation	Leading Edge, PWM, Trailing Edge
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	12.5 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	150 W
Output Voltage	12 V

### Protection Category

IP Rating	IP66
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, 3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547
---------------------	---