



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 5223514-3
2MM FB,IS,ASY,096,SIG,HDR,SL




TE Part # 223513-3
2MMFB,IS,ASY,096,SIG,HDR,SL



TE Part # 5536514-3
2MMFB,ASY,096,SIG,HDR,EN,4.25




TE Part # 5536504-3
2MM FB,ASY,096,SIG,HDR,EN,6.50




TE Part # 5536501-3
2MM FB,ASY,96,SIG,HDR,SL,4.25



TE Part # 5536513-3
2MM FB,SIG,PIN,ASY,096,4.25



TE Part # 5536536-3
2MMFB,ASY,096,SIG,HDR,SL,3.20



TE Part # 536504-3
2MM FB,ASY,096,SIG,HDR,EN,6.50


Customers Also Bought



TE Part #1-534206-0
20 MODII VRT DR CE 100/115



TE Part #5499913-1
A/L UNIV HDR 10P RA SHT LAT



TE Part #5530843-2
CONN SEC II 15 POS 100C/L



TE Part #5554501-1
RCPT ASSY,24 POS,V/M,SCR LK

Documents

Product Drawings
2MM FB,ASY,096,SIG,REC,SL,3.53

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5536510-3_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5536510-3_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5536510-3_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Application Specification

English

Agency Approvals

UL Report

English