

## R 15-EGW-13,5



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 0102
Specification	R 15-EGW-13,5
HARTING eCatalogue	<a href="https://harting.com/09150000102">https://harting.com/09150000102</a>

### Identification

Category	Hoods / Housings
Series	R 15
Type of hood/housing	Screw mounted housing
Description of hood/housing	Angled

### Version

Locking type	Screw locking
--------------	---------------

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Commercial data

Packaging size	10
Net weight	29.16 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021600
eCl@ss	27440224 Shell for circular connectors
ETIM	EC003556
UNSPSC 24.0	39121405