

datasheet for MMS 2020
article number: 972340001



product description:	order number: 972 340-001
description:	Test equipment set for safety applications DIN EN 61010-031, as accessories for measuring instruments. contents: 1 x test tip PRUEF 2700 black (972 319-100), 1 x test tip PRUEF 2700 red (972 319-101), 1 x alligator clip AK 2 B 2540 black (972 405-100), 1 x alligator clip AK 2 B 2540 red (972 405-101), 1 x measuring line MLS WG 100/1 black (934 082-100), 1 x measuring line MLS WG 100/1 red (934 082-101)
typ:	MMS 2020
system:	4mm safety system
order number:	972 340-001
clamping range:	30mm
technical data	
measurement category	CAT III // AK 2 B 2540, PRUEF 2700: CAT II
norm	DIN EN 61010-031
pin dimensions	4mm
type of contact:	pin (spring-loaded)
type of termination:	4mm diameter pin
cable type:	LEH-XY
cable specification:	highly flexible lead
wire stranding:	259 x 0,07
rated voltage:	AC/DC 1000 V
cable length:	100cm
conductor size:	1mm ²
cable material:	PVC
cable color:	each article in black and red.
environmental conditions:	
temperature range:	-15 °C to +70 °C