

## FEATURES

- Tested for 30,000 movements.
- 3 steel articulated arms with vibration proof, friction knuckle
- Joint friction adjustment if required
- Anti-glare visor

# RS PRO LED Machine Light, 230 V, 60 W, Articulated, 750mm Reach, 750mm Arm Length

RS Stock No.: 743-937



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From RS Pro, this bench task light is the ideal lighting system for those engaging in high concentration, high detail work. With an adjustable base, and an arm with four points of articulation, the operator can ensure there is bright, clear light source where it is needed. This has the advantage of ensuring shadow free work and reducing eye strain. With friction free joints, the arm adjusts easily and retains its position. It also has resistance to vibration, which means it is suitable for work around heavy machinery.

## General Specifications

<b>Lamp Type</b>	Incandescent – self ballasted fluorescent – LED Retrofit Lamp
<b>Light Style</b>	Articulated Arm
<b>Lamp Supplied</b>	No
<b>Integral transformer</b>	No
<b>Lamp Base</b>	E27 Edison Screw
<b>Base Type</b>	Universal Base – can be horizontal or vertical mounted
<b>Shield Fitted</b>	Yes
<b>Switch Fitted</b>	Yes on head
<b>Visor</b>	Moulded Visor complete with handle
<b>Trailing Cable</b>	Not fitted (available as accessory c/w 20mm cable gland)
<b>Finish &amp; Colour</b>	Powder coated Goosewing Grey
<b>Shade</b>	127mm spun aluminium
<b>Arm Type</b>	Articulated

## Electrical Specifications

<b>Mains Plug Type</b>	Euro plug , UK 3Pin Plug
<b>Voltage Rating</b>	230V
<b>Wattage</b>	60W
<b>Number of Bulbs</b>	1

## Mechanical Specifications

<b>Arm Length</b>	750mm
<b>Maximum Reach</b>	750mm

Protection Category

IP Rating

IP 64





