

Selection and ordering data

Version	DT	Order No.	Price per PU	PU (UNIT, SET, M)	PS*/P. unit	PG
General information						
<ul style="list-style-type: none"> For horizontal and vertical mounting Degree of protection: IP20 						
Note	Section	Page				
<ul style="list-style-type: none"> All components of the i-system product range can be used as central inserts and cover plates, see ... Degree of protection IP44 for rockers can be achieved with the <i>IP44 set of seals, for rockers, see ...</i> 	<i>Design / i-system</i>	1/2				
	<i>Design / i-system / Accessories and spare parts</i>	1/43	A	5TG4 324	1	1/10 sets 021
Frames, 80 mm						
Versions						
<ul style="list-style-type: none"> Titanium white (similar to RAL 9010) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 551-0 1 1/10 units 021 Double, 151 mm x 80 mm A 5TG2 552-0 1 1/10 units 021 Triple, 222 mm x 80 mm A 5TG2 553-0 1 1/10 units 021 Quadruple, 293 mm x 80 mm A 5TG2 554-0 1 1/10 units 021 Quintuple, 364 mm x 80 mm A 5TG2 555-0 1 1/5 units 021 Electrical white (RAL 1013) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 581-0 1 1/10 units 021 Double, 151 mm x 80 mm A 5TG2 582-0 1 1/10 units 021 Triple, 222 mm x 80 mm A 5TG2 583-0 1 1/10 units 021 Quadruple, 293 mm x 80 mm A 5TG2 584-0 1 1/10 units 021 Quintuple, 364 mm x 80 mm A 5TG2 585-0 1 1/5 units 021 Aluminum metallic (similar to RAL 9006) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 551-3 1 1/10 units 021 Double, 151 mm x 80 mm A 5TG2 552-3 1 1/10 units 021 Triple, 222 mm x 80 mm A 5TG2 553-3 1 1/10 units 021 Quadruple, 293 mm x 80 mm A 5TG2 554-3 1 1/10 units 021 Quintuple, 364 mm x 80 mm A 5TG2 555-3 1 1/5 units 021 Carbon metallic (similar to RAL 7016) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 551-6 1 1/10 units 021 Double, 151 mm x 80 mm A 5TG2 552-6 1 1/10 units 021 Triple, 222 mm x 80 mm A 5TG2 553-6 1 1/10 units 021 Quadruple, 293 mm x 80 mm A 5TG2 554-6 1 1/10 units 021 Quintuple, 364 mm x 80 mm A 5TG2 555-6 1 1/5 units 021 						
Frames, 80 mm, with labeling field						
Versions						
<ul style="list-style-type: none"> Titanium white (similar to RAL 9010) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 551-1 1 1/10 units 021 Double, 151 mm x 80 mm, horizontal A 5TG2 552-1 1 1/10 units 021 Double, 151 mm x 80 mm, vertical A 5TG2 552-2 1 1/10 units 021 Triple, 222 mm x 80 mm, horizontal A 5TG2 553-1 1 1/10 units 021 Triple, 222 mm x 80 mm, vertical A 5TG2 553-2 1 1/10 units 021 Quadruple, 293 mm x 80 mm, horizontal A 5TG2 554-1 1 1/10 units 021 Quadruple, 293 mm x 80 mm, vertical A 5TG2 554-2 1 1/10 units 021 Electrical white (RAL 1013) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 581-1 1 1/10 units 021 Double, 151 mm x 80 mm, horizontal A 5TG2 582-1 1 1/10 units 021 Double, 151 mm x 80 mm, vertical A 5TG2 582-2 1 1/10 units 021 Triple, 222 mm x 80 mm, horizontal A 5TG2 583-1 1 1/10 units 021 Triple, 222 mm x 80 mm, vertical A 5TG2 583-2 1 1/10 units 021 Quadruple, 293 mm x 80 mm, horizontal A 5TG2 584-1 1 1/10 units 021 Quadruple, 293 mm x 80 mm, vertical A 5TG2 584-2 1 1/10 units 021 Aluminum metallic (similar to RAL 9006) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 551-4 1 1/10 units 021 Double, 151 mm x 80 mm, horizontal A 5TG2 552-4 1 1/10 units 021 Double, 151 mm x 80 mm, vertical A 5TG2 552-5 1 1/10 units 021 Carbon metallic (similar to RAL 7016) <ul style="list-style-type: none"> Single, 80 mm x 80 mm A 5TG2 551-7 1 1/10 units 021 Double, 151 mm x 80 mm, horizontal A 5TG2 552-7 1 1/10 units 021 Double, 151 mm x 80 mm, vertical A 5TG2 552-8 1 1/10 units 021 						
Note						
Our free labeling tool can help you create individual labeling fields. Download at: www.siemens.com/labeling-tool						



5TG2 551-0



5TG2 551-1