

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200060560](#)
Status: **Active**
Overview:
Description: Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 0.34mm² Black PVC Cable, 2.0m (6.56') Length

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series [120006](#)
 Connector End A Micro-Change (M12)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview microchange_m12_connectors
 Product Name Micro-Change (M12)
 Protocol N/A
 Region Europe
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 883906067984

Physical

Cable Diameter 5.40mm (.213")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Male-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Net Weight 102.100/g
 Orientation Straight to Pigtail
 Poles 4
 Temperature Range - Operating -30° TO +80°C
 Wire Size AWG 22
 Wire/Cable Type UL 2464

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V

Material Info

Engineering Number 804006E03M020

Reference - Drawing Numbers

Sales Drawing 1200659185-000

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000408918_00_000.pdf

CER_4000410285_00_000.pdf

Search Parts in this Series

[120006](#) Series