





PRODUCT NO. 61729

1 1



213

TYPE"1" FULL BACK



1

TYPE"2" PARTIAL BACK

NOTES:


- 1. MATERIAL: SHIELD & CONTACTS: COPPER ALLOY HOUSING: UL 94V-0 THERMOPLASTIC. COLOR: SEE PRODUCT NUMBER CODE.
- 2. PLATING: SEE PRODUCT NUMBER CODE.
 - SHIELD: BRIGHT TIN NICKEL UNDERPLATE.
- 3. DATUMS & BASIC DIMENSIONS TO BE DETERMINED BY CUSTOMER

5 I

4. RECOMMENDED BOARD THICKNESS IS 1.57 mm (.062)

4

- 5. PACKING STANDARD GS-14-920 WILL BE APPLIED FOR LEAD FREE $\ensuremath{\text{P/N}}\xspace's$
- 6. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN $\rm GS-22-008$
- 7. FOR LEAD FREE P/N'S, THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TERMERATURE FOR 40 SECONDS IN A CONVECTION, INFRO-RED OR VAPOR PHASE REFLOW OVEN.
- 8. THE PART CAN BE USED FOR PIP PROCESS.



6

А

В

С

D

form no. 7530-001-104

D

3