## on-off valve MS6-EM1-1/4-S Part number: 541272

Manual, with silencer, direction of flow: from left to right.

## **Data sheet**

Feature	Value
Design structure	Rotary slide valve
Type of actuation	manual
Exhaust-air function	not throttleable
Type of piloting	direct
Valve function	3/2 bistable
Operating pressure	0 18 bar
C value	10.7 l/sbar
b value	0.56
Standard nominal flow rate	3,000 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
	Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Materials note	Free of copper and PTFE
	Conforms to RoHS
Medium temperature	-10 60 °C
Ambient temperature	-10 60 °C
Food-safe	See Supplementary material information
Mounting type	Optional
	Line installation
	with accessories
Assembly position	Any
Flow direction	non reversible
Product weight	655 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	Integrated silencer
	Non-ducted
Material seals	TPE-U(PU)
Material housing	Aluminium die cast



**FESTO**