



## DCF899NT

### XR 18V BRUSHLESS 3 Sp High Torque Wrench (Naked in TSTAK)

#### Selling Proposition

- Latest generation 18V BRUSHLESS XR Li-Ion High Torque Wrench
- Powerful fan cooled motor delivers up to 950Nm of torque and 2400 impacts per minute for heavy duty fastening applications
- Up to 1625Nm of "breakaway" torque ensures removal of the tightest bolts
- 3 Speed and torque settings gives you the control to best suit your application
- 1/2" (13 mm) square drive with detent pin allows for more efficient torque delivery and excellent socket retention
- Bright white LED with delay feature for improved visibility and flashlight functionality

#### Standard Equipment

- TSTAK heavy-duty kitbox
- Battery and charger sold separately

#### Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Max Torque	135/400/950 Nm
Power Output	610 Watt
No Load Speed	0 – 400/1200/1900 rpm
Impacts per Minute	0 – 2400 ipm
Max. Bolt Diameter	M20
Bit Holder	1/2"
Weight	2.62 kg