



Extension Cable GdV 5x1.5mm² 5m T15-T15 IP55 black



Item No.: 037020476 05 15 1
EAN Code: 7611007159726

Description

Extension Cable GdV H07RN-F 5G1.5mm² black, cable length 5m, 1st side T15 IP55 plug orange, 2nd side T15 IP55 coupling orange

Specifications

Type	Extension Cable
Brand	STEFFEN
Model	GdV
Cable Type	H07RN-F
Number of Conductors	5
Conductor Cross-Section	1.5 mm ²
Cable Length	5 m
Cable Colour	Black
Outer Sheath Material	Reinforced Rubber
Core Insulation Material	Rubber Compound
Socket Type	Type 15 IP55
Increased Touch Protection	No
Plug Type	Type 15 IP55
Rated Current	10 A

Rated Voltage	400 V
Rated Frequency	50 - 60 Hz
Rated Power	6900 W
Halogen-Free	No
UV Resistance	Yes (not tested)
Application	Indoor, Outdoor
K2 Suitable for Construction Sites	Yes
IP Rating	IP55
Operating Temperature Range	flexing: -25...+60 °C
Product Height	90 mm
Product Width	250 mm
Product Depth	250 mm
Net Weight	1.280 Kg
Packaging	Open with Sleeve
