

PRODUCT DATASHEET

DP HOUSING 1200 2x Lamp IP65

DAMP PROOF HOUSING | Damp-proof luminaire for T8 LED lamps



PRODUCT BENEFITS

- Prewired for easy installation of tubular AC LED lamps
- Robust housing
- Easy and quick installation
- 5 years guarantee

PRODUCT FEATURES

- Luminaire housing, available for 1 or 2 T8 LED lamps
- Type of protection: IP65
- Suitable for SubstiTUBE EM/UN and SubstiTUBE Connected



TECHNICAL DATA

Electrical data

Nominal voltage	220...240 V
Mains frequency	50/60 Hz

Light technical data

Beam angle	105.00 °
------------	----------

Dimensions & weight



Length	1265 mm
Width	115.0 mm
Height	86.0 mm
Product weight	1635.00 g

Colors & materials

Body material	Polycarbonate (PC)
Housing color	Gray
Product color	Gray
Housing color	Gray
Cover material	Polycarbonate (PC)

Temperatures & operating conditions

Ambient temperature range	-30...+40 °C
---------------------------	--------------

Lifespan

Lifespan L70/B50 at 25 °C	- h
Lifespan L80/B10 at 25 °C	- h
Lifespan L90/B10 at 25 °C	- h

Additional product data

Mounting type	Suspended/Surface
Mounting location	Ceiling / Wall
Equipped with lamp	No

Capabilities

Dimmable	No
Type of connection	Screwless terminal, 3-Pole
Holder designation	G13
Ball shot safe	No

Certificates & standards

Protection class IK (shock resistance)	IK08
Protection class	I
Type of protection	IP65
Luminaire with limited surface temperature, class "D"	No
Standards	CE

EQUIPMENT / ACCESSORIES

- All required accessories included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075089846	Folding carton box 1	65 mm x 1278 mm x 114 mm	1705.00 g	9.47 dm ³
4058075089853	Shipping carton box 8	1285 mm x 235 mm x 276 mm	8219.00 g	83.35 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

- ▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.