



## SE-15-24








### General Purpose Bow Saw with 51 Toothed Blade 24"



#### PRODUCT DETAILS

- Teeth points high-frequency, heat induction hardened for long-lasting performance
- 51 supplied with peg tooth blade for dry wood, 23 supplied with raker tooth blade for green wood
- The knuckle protector provides comfort and safety
- Powder painted steel tube for excellent rust protection
- SE-16 with pointed nose for better access in tight areas
- Professional bow saw for all types of work, especially in building, gardening, farming and forestry applications

#### PRODUCT ATTRIBUTES

Product							
SE-15-24	607 mm	24 in	170 mm	6-3/4 in	51	675 g	23.8 oz

Follow the Fish!

