

BMP™21 Label Printer



The BMP™21 Portable Label Printer is an all-in-one labeler for voice/data comm, electrical and general industrial crews. With label materials designed specifically for harsh environments, the BMP™21 portable printer can quickly and easily create clear, legible labels that stay stuck for years - despite extreme temperatures and curved or highly textured surfaces.

Specifications

RoHS Compatibility: Yes

Print Resolution: 203 dpi

Print Technology: Thermal Transfer

Application(s): Panel Identification, Facility, Wire & Cable Marking, Data Communications Labeling, General & Industrial Labeling, Safety & Maintenance Identification

Keyboard: ABC

Max Labels Per Day: 50 labels/day

Display: LCD

Max Label Width: 0.750"

Max Print Width: N/A

Max Roll Length: 21'

Text Sizes: 6 (6 to 40 point font)

Color Capability: Single Color Printing

Multi-Line Print: Yes

Print Rotation: No

Serialization: Yes

Bar Code Type: 39 and 128

PC Connectivity: No

Peripheral Printing: No

Stand Alone Printing: Yes

Connectivity Options: None

Portability: Yes

Memory: Last label

Power Supply: AC Power (optional), 6 AA's

Materials Supported: Continuous/ 41 Stock parts

Continuous vs Die Cut Labels: Continuous labels only

Weight: 1.66 lbs

Warranty: 12 Months - See Terms and Conditions