



Disposable

SOLO 980

Nitrile | Chlorinated

Thick nitrile disposable gloves that combine dexterity and resistance, suitable for various applications.

SPECIFIC ADVANTAGES



Comfort

- Comfort and flexibility



Productivity

- Pebbled on fingertips for a good grip



Skin protection

- Latex free to reduce the risk of allergies
- Powder free treatment
- Recommended for oily environments in industry



Additional benefits

- Offers reliable protection against a wide range of chemicals like isopropanol and some Skydrol® and Diestone® formulations.

INDUSTRIES

- Automotive/mechanical industry
- Mechanical industry
- Food industry
- Local Authorities (Cleaning)
- Local Authorities (Catering Services)
- Laboratory
- Chemical industry
- Aeronautics industry
- Fishing
- Cosmetics and Pharmaceutical industry

APPLICATIONS

- Food handling
- Food preparation
- Fishing
- Part assembly
- Precision work
- Assembly of small oily parts
- Minor maintenance Tasks
- Precision assembly
- Common cleaning Tasks
- Manufacturing of medicines



CHEMICAL PROTECTION
TYPE B

EN ISO 374-1



TYPE B
JKPT

EN ISO 374-5



VIRUS

EN 421



CATEGORY 3



0334

DEXTERITY

EN ISO 21420:
5/5



BfR XXI



Disposable

SOLO 980

Nitrile | Chlorinated

LEGENDS

EN ISO 374-1



TYPE B

CHEMICAL RISKS

J: n-Heptane
K: Sodium hydroxide 40%
P: Hydrogen peroxide 30%
T: Formaldehyde 37%

EN 421



RADIOACTIVE CONTAMINATION

EN ISO 374-5



VIRUS

MICRO-ORGANISMS

Protection against bacteria, fungi and virus



FOOD CONTACT

BfR XXI

PRODUCT DETAILS

Interior finish	Chlorinated
Exterior finish	Pebbled
Material	Nitrile
Cuff characteristic	Rolled Cuff
Colour.s	Blue
Length (cm)	30
Thickness (mm)	0.20
European sizes	6 7 8 9 10 11
AQL Liquidproofness	1.5

LOGISTIC DETAILS

Packaging	50 gloves/box 500 gloves/carton
-----------	------------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/10/24/2331
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France