

## 42U Adjustable Depth Open Frame 4 Post Server Rack Cabinet - Flat Pack w/ Casters, Levelers and Cable Management Hooks

Product ID: 4POSTRACK42



The 4POSTRACK42 42U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 42U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1320lbs (600kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete rack solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securing the rack to the floor if needed, providing you with many options to customize the rack to fit your environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

### Features

- 42U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1320lbs (600kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

<b>Hardware</b>	Warranty	2 Years
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	4-Post
	Special Features	Adjustable Mounting Rails
		Base Plate with Floor-Anchoring Holes
		Built-in Cable Management
		Casters (Included)
Grounding Lug(s)		
Leveling Feet		
Easy Assembly		
U-Height	42U	
Wallmountable	No	
<b>Performance</b>	Weight Capacity (Stationary)	1326 lb [600 kg]
<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
<b>Product Measurements</b>	Maximum Mounting Depth	40 in [101.7 cm]
	Minimum Mounting Depth	22 in [56 cm]
	Product Height	77.6 in [197 cm]
	Product Height with Casters	80.3 in [204 cm]
	Product Length	3.4 ft [1 m]
	Product Width	23.8 in [60.4 cm]
	Weight of Product	85.1 lb [38.5 kg]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Package Height	6.7 in [17 cm]
	Package Length	6.7 ft [2 m]
	Package Width	10.6 in [27 cm]

	Shipping (Package) Weight	90.6 lb [41 kg]
<b>What's in the Box</b>	Included in Package	<ul style="list-style-type: none"> <li>2 - Left Vertical Rail</li> <li>2 - Right Vertical Rail</li> <li>2 - Base Bracket</li> <li>8 - Corner Section</li> <li>4 - Center Section</li> <li>2 - Top Bracket</li> <li>50 - M8 Bolt</li> <li>50 - M8 Washer</li> <li>1 - M6 (10mm) Wrench</li> <li>1 - M8 (13mm) Wrench</li> <li>6 - Phillips Screwdriver</li> <li>4 - M6 grounding wire bolts (short)</li> <li>4 - M6 grounding wire lock washers</li> <li>50 - M6 Cage Nut</li> <li>50 - PVC Cup Washer</li> <li>50 - M6 Phillips Head Screw</li> <li>24 - Cable Management Hook</li> <li>24 - Hook Mounting Screw</li> <li>4 - Casters</li> <li>4 - Leveling Feet</li> <li>16 - M6 Screw</li> <li>16 - M6 Flat Washer</li> <li>16 - M6 Flange Nut</li> <li>4 - Grounding Wires</li> </ul>

Product appearance and specifications are subject to change without notice.