



---

**PRODUCT-DETAILS****SPL25/M25/C90****90D NPB FITTING M25 25MM-MET**

---

**General Information**

Extended Product Type	SPL25/M25/C90
Product ID	7TCA296030R0212
EAN	5020963019685
Catalog Description	90D NPB FITTING M25 25MM-MET
Long Description	90 Degree Conduit Fitting with Fixed External Male Threads, Conduit Size 25 Millimeters / 3/4 Inch, Thread Size M25, Nickel-Plated Brass

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

---

**Ordering**

EAN	5020963019685
UPC	786210246970

**Technical**

Number of Batteries	0
Color	Metallic
Material	Brass
Size	NC 25mm

**Environmental**

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

**Container Information**

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963019685
Package Level 1 Height	11.81 in 300 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

**Certificates and Declarations**

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

**External Classifications and Standards**

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

**Categories**

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

