

## General Information

<b>Extended Product Type:</b>	332ERU6W
<b>Product ID:</b>	2CMA101313R1000
<b>EAN:</b>	7392696013130
<b>Catalog Description:</b>	Panel mounted socket outlets, 3P+E, 32A, 380 ... 415 V
<b>Long Description:</b>	Panel mounted socket outlets, 3P+E, 32A, 380 ... 415 V

## Additional Information

<b>Additional Information:</b>	3P+E
<b>Cable Cross-Section:</b>	2.5 ... 6 mm <sup>2</sup>
<b>Color:</b>	Red
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	Czech Republic (CZ)
<b>Customs Tariff Number:</b>	85366990
<b>Data Sheet, Technical Information:</b>	2CMC700006C0201
<b>Declaration:</b>	2CMC700005D0001
<b>Declaration of Conformity - CE:</b>	2CMC700005D0001
<b>Degree of Protection:</b>	IP67
<b>E-number:</b>	2417708
<b>EAC Certificate:</b>	RU C-CZ.ME77.B.02742
<b>EAN:</b>	7392696013130
<b>ETIM 5:</b>	EC001321 - CEE socket outlet
<b>ETIM 6:</b>	EC001317 - Panel-mounted CEE socket outlet
<b>Enclosure Material:</b>	Plastic (PA)
<b>Environmental Information:</b>	2CMC700001D0002
<b>Frequency (f):</b>	50 Hz 60 Hz
<b>Function:</b>	Socket outlet for panel mounting
<b>Gross Weight:</b>	0.23 kg
<b>Housing Material:</b>	Plastic (PA)
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Invoice Description:</b>	Ind. P&S#332ERU6W
<b>Minimum Order Quantity:</b>	10 piece
<b>Number of Poles:</b>	4
<b>Package Level 1 EAN:</b>	7392696021890
<b>Package Level 1 Gross Weight:</b>	2.3 kg
<b>Package Level 1 Height:</b>	442 mm
<b>Package Level 1 Length:</b>	192 mm
<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	94 mm
<b>Product Main Type:</b>	ERU
<b>Product Name:</b>	Panel mounted socket outlet
<b>Product Net Depth:</b>	101 mm
<b>Product Net Height:</b>	98 mm
<b>Product Net Length:</b>	101 mm
<b>Product Net Weight:</b>	0.23 kg

<b>Product Net Width:</b>	85 mm
<b>Protection Type:</b>	Watertight
<b>Rated Current (I<sub>n</sub>):</b>	32 A
<b>Rated Voltage (U<sub>r</sub>):</b>	380 ... 415 V
<b>SEMKO Certificate:</b>	1616295
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Panel mounted socket outlets, 3P+E, 32A, 380 ... 415 V
<b>Size:</b>	101x99x104
<b>Standards:</b>	IEC 60309-1 IEC 60309-2
<b>UNSPSC:</b>	39120000
<b>Clock Position Of Grounding Contact:</b>	6 hour
<b>RAL Number:</b>	RAL 7012 - Basalt Grey