









LOC	DIST	REVISIONS						
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A1	REVISED PER ECO-11-004820	28MAR2011	RK	HMR	
			A2	REVISED PER ECO-12-003780	25FEB2012	HVG	DD	
			B	REVISED PER ECR-13-008007	17SEP2013	RS	DD	



- 1 MATERIAL: HOUSING: LCP, COLOR: BLACK.
- 2 CONTACTS: BRASS.
FINISH: 2.54µm MIN MATTE TIN OVER NICKEL (ENTIRE POST).
HOLDDOWN: COPPER ALLOY.
FINISH: 2.54µm MIN MATTE TIN OVER NICKEL.
- 3 VACUUM PICK-UP
BUTTON: POLYIMIDE.
4. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
- 5 RECOMMENDED PC BOARD THICKNESS OF 1.57.
6. TAPE AND REEL PACKAGING PER EIA-481 SPEC.
7. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS).




10.94	3.19	27.65	21.90	12.46	12.46	4	2106053-6
9.20	3.20	24.15	18.40	8.96	12.46	3	2106053-4
7.44	3.18	20.65	14.90	8.96	8.96	2	2106053-2

DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: HM VAN SCHOCK 23JAN2009	TE Connectivity				
DIMENSIONS:		CHK: A. BUCHER 23JAN2009					
mm		APVD: A. BUCHER 23JAN2009	NAME				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	ASSEMBLY, VERTICAL SMT HEADER, SLIMSEAL SSL CONNECTOR				
0 PLC ±0.2		108-2391					
1 PLC ±0.15		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO				
2 PLC ±0.1		114-13261					
3 PLC ±0.1		WEIGHT	A100779C=2106053				
4 PLC ±0.1		CUSTOMER DRAWING					
ANGLES FINISH		SCALE 4:1	SHEET 1 OF 2 REV B				
1 2 3							

LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-



RECOMMENDED PC BOARD PAD LAYOUT, COMPONENT SIDE
DIMENSIONS APPLY TO ALL POSITIONS UNLESS OTHERWISE NOTED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: HW VAN SCO	23JAN2009	 TE Connectivity	
DIMENSIONS:		CHK: A. BUCHER	23JAN2009		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: A. BUCHER	23JAN2009	NAME	
	0 PLC ±0.2	PRODUCT SPEC		ASSEMBLY, VERTICAL SMT HEADER, SLIMSEAL SSL CONNECTOR	
	1 PLC ±0.15	108-2391			
	2 PLC ±0.1	APPLICATION SPEC			
	4 PLC ±0.1	114-13261			
ANGLES ±0°		WEIGHT		SIZE CAGE CODE DRAWING NO	
		-		A100779C=2106053	
MATERIAL	FINISH	CUSTOMER DRAWING		RESTRICTED TO	
				-	
		SCALE 4:1		SHEET 2 OF 2	
				REV B	