



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Multi-directional head
Product compatibility	XCKJ
Associated body	ZCKJD35H29 ZCKJ1H29 ZCKJ8H7 ZCKJ21 ZCKJ6 ZCKJ9 ZCKJD39 ZCKJ9H7 ZCKJ2H7 ZCKJ11H7 ZCKJ6H7 ZCKJ5 ZCKJ21H29 ZCKJ5H7 ZCKJ8H29 ZCKJD31 ZCKJD37H29 ZCKJ7H7 ZCKJ2H29 ZCKJ11 ZCKJD37H7 ZCKJD31H7 ZCKJ1 ZCKJ7H29 ZCKJ6H29 ZCKJ21H7 ZCKJ7 ZCKJ11H29 ZCKJD39H29 ZCKJD31H29 ZCKJ8 ZCKJD37 ZCKJD35H7 ZCKJ9H29 ZCKJD35 ZCKJ1H7 ZCKJ2 ZCKJD39H7 ZCKJ5H29
Movement of operating head	Multi-directional
Type of operator	Spring rod spring return
Type of approach	Multi-directional approach

### Complementary

Switch actuation	By any moving part
Positive opening	Without
Net weight	0.125 kg
Head material	Metal

## Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Low temperature

## Packing Units

Package 1 Weight	134 g
Package 2 Weight	3.595 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------